

# **Technical Data Sheet**

## NightGlo NG-200 Phosphorescent Pigment

#### General description

DayGlo® NG-200 is a zinc sulfide compound that responds quickly to excitation by daylight, incandescent, fluorescent or ultraviolet lights.

The pigment emits a bright green phosphorescence shade with high initial brightness and afterglow – the effect of which depends on pigment concentration, surface area and amount of radiant energy absorbed.

NightGlo NG-200 can also be mixed with certain transparent pigments or colorants, such as DayGlo fluorescent dyes and pigments. This combination can create some very attractive special effects.

Recommended loading is a 1 to 10 ratio of fluorescent to phosphorescent pigment.

Available Colors		
<b>Product Code</b>	Color	
NG-200	NightGlo	

#### Packaging:

5 Gallon Pail = 55 lb (25kg)

#### Storage & shelf life:

120 months when kept in closed original packaging in a dry place at ambient temperature.

#### Safety & regulatory:

Safety Data Sheet available on request.


### **Applications**

Plastic resins – Acrylics, Nylons, Polystyrene, Polyolefins, Vinyl

Physical properties		
Delivery form	Powder	
Emission color	Green	
Afterglow color	Green	
Daylight body color	Slightly Yellow	
Specific gravity	4.1	
Particle size	18-25 μm	
Melting point	1830 degrees C	
Mohs hardness	3.0	




#### **Emission Spectrum**



#### **Persistence Curve**

DIN67510, Part 1 (Xenon Excitation – 5 min. @ 1,000 Lux, 22°C ± 3°C)



10 min. (mcd/m²)	60 min. (mcd/m²)	Time to reach 0.32 mcd/m <sup>2</sup>
≥26	≥2.5	≥280 min.

#### Handling

When handling phosphorescent pigment, some precautions should be taken when:

- Working with strong acids since this can cause dissolution of phosphorescent pigments. In the presence of high relative humidity and sunlight, phosphorescent pigments can exhibit darkening.
- It is not recommended to mill this product since this will degrade the phosphorescence due to breakdown
  of the crystal structure of the phosphorescent pigment. Mild stirring should be used to incorporate NG-200
  into a vehicle.

The addition of colorless extenders or colored pigments will reduce the intensity of the phosphorescence. Testing is recommended in the intended application to determine suitability.

Recommended concentration is approximately 10% by weight.

**Disclaimer:** Our technical advice, information, statements, whether given verbally, in writing, or in the form of test results, is offered for your guidance without warranty. No warranty for fitness for a particular purpose is made. This also applies where protective rights of third parties are involved. It does not release the user from obligation to test the suitability of the products and formulas for the intended process and applications. Our guarantee is limited to the consistent quality of our product.